

FEATURES

- 18 piece LED
- 3 step dimmer (low, medium high)
- Folding task light
- Voltages: DC5v, 0.5A, 1.8w
- Light Specification: LED 18 piece
- Colour Temp: 5000-5500 Kelvin
- Switch: Touch switch with a 3 step dimmer
- Charging time: 3-4 hours
- Usage time: up to 6 hours
- USB Cable: 1.5m for use with computers/laptops and another USB portal

RS PRO Slim-Line LED Task Lamp

RS Stock No.: 136-3723



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Features:

- 18 piece LED
- 3 step dimmer (low, medium high)
- Folding task light
- Voltages: DC5v, 0.5A, 1.8wLight Specification: LED 18 piece
- Colour Temp: 5000-5500 Kelvin
- Switch: Touch switch with a 3 step dimmer
- Charging time: 3-4 hoursUsage time: up to 6 hours
- USB Cable: 1.5m for use with computers/laptops and another USB portal

Electrical Specifications

Light Source	18 LEDs
Energy Consumption	1.8w
Lumens	180
Colour Temperature	5300k
CRI	90
Voltage	5V

Classification

eCl@ss (Version)	
UNSPSC (Version)	

Approvals

Declarations	CE/RoHS/REACH
Hazardous Area Certification	N/A
Standards Met	CE/RoHS/REACH