

Random Orbit Polisher LXT®

DPO600

18V • 150 mm • 0 – 780 min⁻¹

Professional cordless polisher with eccentric orbit

Powerful, battery-powered polisher with 150 mm Velcro fastening for polishing cars, boats and other solid surfaces. Cam and forced rotation with 5.5 mm eccentric orbit makes polishing easy and efficient. Adjustable rotation speed 180 – 780 per min and oscillation speed 0 – 6 800 min⁻¹.



Technical specifications

Brushless Motor	✓
Voltage LXT	✓
Nominal Battery Voltage	18 V
No load speed	0 - 600 / 0 - 780 min ⁻¹
Orbits per Minute	0 - 6800 min ⁻¹
Sanding Disc Diameter	150 mm
Sanding Orbit Diameter	5,5 mm
Sound Power Level (L _{WA})	94 dB(A)
Sound Pressure Level (L _{pA})	83 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes), Polishing	10,0 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Tool weight with battery	3,1 - 3,6 kg
Product Dimensions (L x W x H):	530 x 148 x 126 mm

User benefits

- Soft start for smooth start-ups
- Ergonomic soft grip handle provides increased comfort
- Recessed lock-on button for continuous use
- Constant speed control maintains constant speed under load
- Variable speed control dial enables user to match the speed to the application for greater versatility
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Optional AC

162258-0 Side Handle		193288-0 Felt pad 150mm	
197894-3 Sponge Pad 150 mm		197922-4 Hook & Loop Pad 125 mm	
197928-2 Hook & Loop Pad 150 mm		198043-5 Grip 36 set	
199424-6 Round Hook and Loop Wool		D-74653 Sponge Pad 125 mm	
P-21727 Sponge pad 150 mm		P-21733 Sponge pad 150 mm	
P-21749 Sponge pad 150 mm			

Other

User manual

Parts drawing