Mitre Saw LXT®

DLS600

18V • 165 mm • 5 000 min^{-1}

A light and compact cordless saw for trim work

A light and accurate battery-powered mitre saw designed for trim work in renovation and construction projects. Cutting capacity of 46 x 92 mm, bevel and mitre cutting left and right.



Technical specifications

Brushless Motor	✓
Capacity 90°	46 x 92 mm
Nominal Battery Voltage	18 V
Voltage LXT	✓
No load speed	5000 min^{-1}
Capacity 45°	46 x 65 mm
Max. Bevel Range (Left)	46 / 46 °
Max. Mitre Range (Left)	52 / 52 °
Blade Diameter	165 mm
Bore Size (Arbor Diameter)	20 mm
Sound Power Level (L_{WA})	97 dB(A)
Sound Pressure Level (L_{pA})	90 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s²
Vibration Uncertainty (K Factor)	1,5 m/s²
Laser Class	2M

User benefits

- Brushless maintenance-free and long-life motor
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Lightweight for easy portability
- Built-in LED light illuminates the line of cut for increased accuracy
- Large aluminium base supports large stock for efficient cutting
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com

Related products

Optional AC

122470-4
Horizontal Vice Assembly



122472-0
Repetitive Cut Stop



122536-0
Vertical Vice Assembly



122884-7
Dust Bag



126695-2
Sub Fence Assembly



192621-3
Holder Set



762001-3
Triangular Rule

783203-8
Hex Wrench 5 Mm



783208-8
Hex Wrench 2,5 mm



Other

User manual

Parts drawing