

VARTA Night Cutter Pro F30R Rech. Box



Information

- 5 light modes: Turbo, High, Mid, Low and Strobe
- Robust: 2 m impact resistant and IP67 (1 m water depth for 30 min)
- Premium housing out of aviation-grade aluminium
- Rechargeable thanks to USB-C port integrated in the end cap
- Charging and low battery indicator integrated
- Precision Focus: Seamlessly adjustable light beam
- Advanced Safety Technology
- Lanyard included
- Own VARTA product design

Article Details

Ordernumber	18921 101 111
Customs Tariff Number	85131000
Country Of Origin	China
Beam Range	(up to) 280.00 m
Runtime	(up to) 24 h
Total light output	(up to) 1500 lm
Product Diameter mm	42.00
Product Length / Depth mm	169.00
Product Weight g	260.60

Logistical Data

	Content (SU)	GTIN / EAN	Facing (mm)	Depth (mm)	Height (mm)	Weight (kg)
VBE (Selling unit)	1	40 08496 082322	100.00	48.00	230.00	0.36
SK2 (Inner carton 2)						
SK1 (Inner carton 1)						
VSK (Master carton)	4	40 08496 082339	433.00	119.00	134.00	1.59
PAL (Pallet)	392	40 08496 082353	800.00	1,200.00	1,088.00	176.76
Layer / Pallet	Master carton / Layer		Master carton / Pallet		Minimum pieces / shipment unit	
7	14		98		4	

All mentioned products and specifications are subject to change. In case of non-availability of any product or item, VARTA Consumer Batteries GmbH & Co. KGaA cannot be held responsible. Some of the products shown may not be available in all countries. The pictures might be different to the original products. Technical changes and errors reserved.
VARTA Consumer Batteries GmbH & Co. KGaA | Alfred-Krupp-Str. 9 | 73479 Ellwangen | Germany
P.O. Box 1363 | 73473 Ellwangen | Germany | Phone (+49) 7961 83 0 | Fax (+49) 7961 83 440

