

ENCLOSED HOSE REELS FOR COMPRESSED AIR / STEEL

DRFB - SECURITY : Hose reel w/ safety retraction - PU/PVC
Hose



Part number	Length (m)	Flow rate (l/min)	Temperature min/max (°C)	Max. operating pressure (bar)	Profile
DRFB 0812ES	12.00	500.00	-15.00 / 65.00	12.00	European
DRFB 0815ES	15.00	350.00	-15.00 / 65.00	12.00	European
DRFB 1010ES	10.00	900.00	-15.00 / 65.00	12.00	European
DRFB 1012ES	12.00	800.00	-15.00 / 65.00	12.00	European
DRFB 0812BS	12.00	500.00	-15.00 / 65.00	12.00	British
DRFB 0815BS	15.00	350.00	-15.00 / 65.00	12.00	British
DRFB 1010BS	10.00	750.00	-15.00 / 65.00	12.00	British
DRFB 1012BS	12.00	750.00	-15.00 / 65.00	12.00	British
DRFB 0815AS	15.00	350.00	-15.00 / 65.00	12.00	ARO 210
DRFB 1012AS	12.00	800.00	-15.00 / 65.00	12.00	ARO 210

Part number	Dim. A (mm)	Dim. B (mm)	Ø int/ext (mm)
DRFB 0812ES	340.00	302.00	8.00 / 12.00
DRFB 0815ES	370.00	337.00	8.00 / 12.00
DRFB 1010ES	340.00	302.00	10.00 / 14.00
DRFB 1012ES	370.00	337.00	10.00 / 14.00
DRFB 0812BS	340.00	302.00	8.00 / 12.00
DRFB 0815BS	370.00	337.00	8.00 / 12.00
DRFB 1010BS	340.00	302.00	10.00 / 14.00
DRFB 1012BS	370.00	337.00	10.00 / 14.00
DRFB 0815AS	370.00	337.00	8.00 / 12.00
DRFB 1012AS	370.00	337.00	10.00 / 14.00