



Main

Range of product	Harmony Series K
Product or component type	Cam switch operating head
Component name	KAA
Product compatibility	Front mounting bodies 12 and 20 A by Ø 22 mm hole
Cam switch head type	With bezel Ø 29 mm, plastic with metallic finish
Type of operator	Key Ronis 8R1
Rotary handle padlocking	Without
Presentation of legend	With mat black legend
Switching angle	45 °

Complementary

Mechanical durability	1000000 cycles
CAD overall width	29 mm
CAD overall height	29 mm
CAD overall depth	69 mm
Net weight	0.057 kg
Compatibility code	KAA

Environment

Protective treatment	TC
Ambient air temperature for operation	-25...55 °C
Ambient air temperature for storage	-40...70 °C
Shock resistance	30 gn conforming to IEC 68-2-27
Vibration resistance	5 gn conforming to IEC 68-2-6 (f = 10...150 Hz)
IP degree of protection	IP65 conforming to IEC 529 IP65 conforming to NF C 20-010

Offer Sustainability

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------