



product details

80168 DOT-IT LINVARIO SI BLI1

Product description: 80168 DOT-IT LINVARIO SI BLI1
 EAN/ Product: 4008321930828
 Quantity: Blister (BLI) contains 1 Piece (PCE)

Applications	
Operating mode	BATTERY
Type of installation for luminaire	MOUNTING
Dimmable	No
Body material	ALUMINIUM
With on/off switch	Yes
Type of cover	CLEAR
Number of lighting outlets	3
Protection class	III
Accessories	adhesive pad, hook-and-loop pad, magnet
Adjustable	Yes
Type of connection	NOT RELEVANT
IP code	IP20
Cover material	PLASTIC
Reflector material	VAPOURISED PLASTIC
Equipment	LED

General Description	
Disposal	Yes
Standards	CE

Technical - Colors	
Colour of the luminaire	SILVER

Technical - Electrical Data	
Nominal wattage	0.23 W
Nominal voltage	4.5 V
Mains frequency	0 Hz
Nominal current	0.05 A

Technical - Geometries	
Length	178 mm
Width	46 mm
Height	29 mm

Technical - Light Technical Data	
Beam angle	135 °

Packaging units				
EAN	Packaging type and content	Dimensions in h x w x l	Gross weight	Volume
4008321930828	Blister contains 1 Piece	140,000 mm x 42,000 mm x 245,000 mm	182,000 g (0,000 g)	0,766 Cubic dec.
4008321930835	Shipping carton box contains 6 Piece	194,000 mm x 116,000 mm x 255,000 mm	1.216,000 g (0,000 g)	5,972 Cubic dec.



08.02.2010

Subject to change without notice. Errors and omission excepted.
 © 2009 OSRAM GmbH

Page 1 from 1