



Oil



Heavy Duty

Oil-repellent nitrile-coated work gloves, for tasks requiring durability and resistance to sharp materials

- **Enhanced flexibility and durability:** ActivArm® Hycron® 27-810 nitrile-coated gloves offer greater flexibility than PVC-coated gloves, as well as three times more durability than heavy-duty leather alternatives
- **Specialized protection:** Their unique nitrile formulation also ensures robust hand protection against sharp and abrasive materials, as well as oil and grease
- **Enhanced features:** ActivArm® Hycron® 27-810 work gloves feature a long safety cuff, further boosting hand and wrist protection
- **Reduced surface defect risks:** Silicone-free by design, they are ideal for metalworking and motor manufacture, averting any contaminant transfer to paint before painting
- **Elevated comfort:** These ActivArm® gloves' cotton jersey fabric also grants wearers optimal comfort, for less strenuous everyday hand protection



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Chemical

Applications

- Handling metal sheets & panels
- Metalworking & assembly operations
- Press injection molding
- Seizing and finishing structural parts
- Fixing, clipping parts and wire harnesses; connecting devices
- Assembly & inspection of components
- Opening furnaces draining pumps valves or lines and crackers BTX process

Key Features

- **Nitrile formulation:** Flexibility, durability, abrasion resistance*
- **Long safety cuff:** Enhanced hand and wrist protection
- **Silicone-free design:** Assured cleanliness for metal and motor manufacture

**3x more durability than heavy-duty leather alternatives*

Performance Standards & Regulatory Compliance



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COATING COLOR	PACKAGE
ActivArm® Hycron® 27-810	Finishing: Fully Coated Coating Material: Nitrile Liner Material: Cotton Cuff Style: Long safety cuff		10	315 mm	Blue	12 pairs/bag, 12 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699