

3m (10ft) USB-C Charging Cable, 240W (5A) PD EPR, Dual-Layer Silicone/Braided Jacket, USB 2.0 Laptop Charger Cable, USB-IF Certified, Rugged USB-C Charging Cord

Product ID: S2CEPR3M-USB-CABLE



Connect a charger or hub to a USB PD 3.1-enabled device with this USB-C cable, delivering up to 240W EPR Power Delivery and 5A output for fast charging. Clear connector markings ensure quick identification, eliminating guesswork and ensuring full 240W charging support. Always choose the correct Type-C cable for optimal performance and compatibility.

Rugged and Flexible

The USB-C EPR Charging Cable features a silicone inner jacket with a braided nylon exterior for optimal flexibility and wear protection. The durable nickel-plated connectors are designed for frequent daily use, and are rated to operate beyond 20,000 insertion cycles.


Charge Mobile Devices On The Go

Charge a USB-C device with a USB-C wall charger, car charger, or power bank. The 3-meter (9.8-foot) USB Type-C cable is the ideal length for large desks and mobile workstations where extra reach is desired.

Power a Laptop

With up to 5A of output, the USB-C Charger Cord supports up to 240W of Power Delivery to charge a USB-C laptop, or fast charge a tablet or smartphone. To use, connect the cable from a USB-C laptop to a USB-C wall charger.

Certifications, Reports and Compatibility



Applications

Features

- **USB-C EPR CHARGING CABLE:** Rugged and flexible USB-C cable supports Power Delivery 3.1 EPR with up to 240W for high-performance laptops; Designed for reliable, high-power charging; Performance markings on connectors for easy identification
- **USB-IF CERTIFIED:** The USB C Cable with integrated E-marker chip is USB-IF certified, for safe and consistent Power Delivery output to USB-C hosts and peripherals; When using certified cables, reliable performance and compatibility is guaranteed
- **QUALITY CONSTRUCTION:** Dual-layer jacket features a silicone inner layer for optimal flexibility and a braided nylon exterior for rugged use; Designed to withstand frequent $\pm 90^\circ$ bends; Nickel-plated connectors rated beyond 20,000 insertions
- **APPLICATIONS:** Compatible with USB-C Power Delivery-enabled devices; Suitable for charging mobile devices and high-performance laptops such as 16in MacBook Pro/Max M-series; Supports USB 2.0 for general file transfer/sync
- **PERFORMANCE:** 240W/5A PD 3.1 EPR, 48V; Backward Compatible w/140W/100W/60W; USB 2.0 Type-C (480Mbps); 3-meter (9.8-foot) cable; Color: Black; O.D.: 0.18in (4.7mm); Dual-layer Silicone Jacket w/Nylon Braid; NOTE: USB-C video (DP Alt Mode) is not supported

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	Silicone with Braided Nylon

Performance

MTBF	Rated beyond 10,000 insertions
------	--------------------------------

Connector(s)

Connector A	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)
Connector B	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)

Power

Power Delivery	240W
----------------	------

Environmental

Operating Temperature	0 $^\circ$ C - 50 $^\circ$ C (32 $^\circ$ F - 122 $^\circ$ F)
Storage Temperature	-20 $^\circ$ C - 70 $^\circ$ C (-4 $^\circ$ F - 158 $^\circ$ F)

Humidity 5% - 85%

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	30 AWG
Material	ABS
Cable Length	9.8 ft [3 m]
Cable OD	0.2 in [4.2 mm]
Product Length	120.6 in [3063.3 mm]
Product Width	0.5 in [12.3 mm]
Product Height	0.3 in [6.8 mm]
Weight of Product	5.3 oz [151.0 g]

Packaging Information

Package Length	5.0 in [12.8 cm]
Package Width	8.7 in [22.0 cm]
Package Height	0.8 in [2.0 cm]
Shipping (Package) Weight	5.5 oz [157.0 g]

What's in the Box

Included in Package	1 - 3m Braided USB-C Charging Cable M/M
---------------------	---

****Product appearance and specifications are subject to change without notice.***