



Part Number : [1110403304](#)

Product Description : QSFP+-to-QSFP+ Cable
Assembly, 26 AWG, 3.0m Length

Series Number : 111040

Status : Active

Product Category : High-Speed I/O Cable
Assemblies



Documents & Resources

Drawings

[1110403304_sd.pdf](#)

[PK-111040-051-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Contains TBBA; bis(2-ethylhexyl) tetrabromophthalate covering any of the individual isomers and/or combinations thereof per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	High-Speed I/O Cable Assemblies
Series	111040
Description	QSFP+-to-QSFP+ Cable Assembly, 26 AWG, 3.0m Length
Assembly Configuration	Dual Ended Connectors
Connector to Connector	QSFP+-to-QSFP+
Product Name	QSFP Plus,QSFP+
Type	Pluggable
UPC	883906902315

Agency

UL	E72548
----	--------

Electrical

Data Rate	10.0 Gbps
Impedance	100Ω

Physical

Cable Bundling	None
Cable Length	3.0m
Circuits (Loaded)	MSA
Gender	Plug
Lock to Mating Part	Yes
Net Weight	353.693/g
Packaging Type	Bag
Release Style	Pull Tab

Single Ended	No
Wire/Cable Type	Round
Wire Size (AWG)	26

Mates With / Use With

Mates with Part(s)

Description	Part Number
iPass I/O Right-Angle Surface Mount Receptacles	<u>75586</u>

Use with Part(s)

Description	Part Number
QSFP+ Cage Assemblies, Light Pipes, and Heat Sinks	<u>74750</u>
QSFP+ 1x3 Ganged Cage Assemblies and Heat Sink Clips	<u>74768</u>
QSFP+ Ganged Cages and Light Pipe Assemblies	<u>74769</u>