

Exhaust protection VABD-D3-L-GN14

Part number: 8177960

FESTO



Data sheet

 [General operating condition](#)

Feature	Value
Mounting position	optional
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP54
Ambient temperature	-50 °C ... 60 °C
Product weight	3.8 g
Type of mounting	Screw-in Via male thread
Note on materials	RoHS-compliant
Material vent screw	HP PA 12