

FEATURES

- **Sintered Bronze Material:** Provides high durability and wear resistance
- **Flanged Design:** Ensures secure positioning and stability
- **Dynamic Load Rating of 14 N/mm²:** Suitable for dynamic applications
- **Static Load Rating of 50 N/mm²:** Handles high static loads effectively
- **0.62 in Bore Size:** Compatible with a range of shafts
- **0.87 in Outside Diameter:** Fits standard housings
- **1-1/4 in Width:** Offers a broad contact surface for better load distribution

RS PRO 0.62 in Flanged Plain Bearing

RS Stock No: 528-863



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring smooth rotational or sliding motion. Made from sintered bronze, it offers excellent durability and resistance to wear, making it ideal for high-load environments. The flanged design ensures secure positioning, enhancing stability and performance.

General Specifications

Bore Size	0.62 in
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	0.87 in
Width	1-1/4 in

Approvals

Standards/Approvals	ISO 9001:2008, UKAS 001
---------------------	-------------------------

