



QO120

MINIATURE CIRCUIT BREAKER 120/240V 20A



[Download your QO120 datasheet](#)



[Characteristics](#) | Documents & Downloads

Main Hide

Product or component type	Miniature circuit-breaker
Range of product	QO
[In] rated current	20 A
Product certifications	CSA UL listed
[Ue] rated operational voltage	120/240 V AC
Mounting mode	Plug-in
Poles description	1P
Short-circuit current	10 kA
Number of spaces required	1
Circuit breaker type	Standard
Circuit breaker application	HACR and Switching Duty rated
Electrical connection	Pressure plate
AWG gauge	AWG 14...AWG 8 (copper or aluminium)
Accessory / separate part type	None

Offer Sustainability Hide

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available download Product environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty Hide

Period	18 months
---------------	-----------