


## FEATURES

- **UV Resistant:** Ensures longevity and reliability in outdoor environments.
- **High Tensile Strength:** Supports up to 34 kg, providing robust cable management.
- **Temperature Resistant:** Operates effectively up to 85 °C, suitable for various conditions.
- **Flame Retardant:** Meets UL 94 V-2 standards, enhancing safety in fire-prone areas.
- **Wide Compatibility:** Accommodates bundles up to 74 mm in diameter, offering versatility.

## RS PRO UV Protected Cable Tie, 300 mm Nylon

RS Stock No: 656-118



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

These RS PRO UV Protected Cable Ties are designed for secure and reliable bundling of cables and wires. Made from durable nylon, they are ideal for both indoor and outdoor use, providing excellent resistance to UV radiation. With a maximum bundle diameter of 74 mm, these cable ties offer flexibility and strength for various applications.

### General Specifications

Colour	Black
Product Type	Cable Tie
Sub Type	UV Protected Cable Tie
Tensile Strength	34 kg

### Protection Category

Fire Behaviour	UL 94 V-2
UV Resistant	Yes

### Mechanical Specifications

Length	300 mm
Material	Nylon
Maximum Bundle Diameter	74 mm
Width	4.8 mm

### Operation Environment Specifications

Maximum Operating Temperature	85 °C
-------------------------------	-------

### Approvals

Standards/Approvals	ABS 15-TA1338482-PDA, cULus E97527, RoHS, UL94V-2
---------------------	---