


**ENGLISH** 

## **Datasheet**

## RS 30 $\rightarrow$ 120 V ac/dc 98dB Panel Mount Continuous Internal Piezo Buzzer

RS Stock 780-0709





## Features:

· Colour: Black

Housing material: ABS

Panel mounted

All data at 25°C unless otherwise specified.

SPECIFICATIONS	Piezo Indicator
Operating Voltage	30-120VDC/AC
Rated Current at rated voltage max	17mA
Sound Output at 30cm, at rated voltage	≥98dB
Resonant Frequency	2800±500Hz
Tone	Continuous
Operating Temperature	-20 ~ +60°C
Storage Temperature	-30 ~ +70°C
Weight	<b>4</b> 3g
Drive Type	Internal

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.