




Technical Data

22.01.2024

Heat Shrinkable Tubing 3:1 adhesive lined on a reel
TAN32

TAN32-12/4

Article Number 318-60012



Material: Polyolefin, cross-linked (PO-X)
Colour: Black (BK)
Adhesive: EVA hot melt adhesive

Supplied Ø D min.: 12.00 mm
Recov. Ø d max.: 4.00 mm
Wall (WT): 1.65 mm
Shrink Ratio: 3:1
Longitudinal Change After Shrinkage: -10% max.
Min. Shrink Temperature - °C: +110 °C

Test Method

Flammability: UL 224 VW-1
Operating Temperature : -55 °C to +125 °C
Heat Shock Test: 4h/250°C
Behaviour at Heat Shock: not fluid, not dripping, not cracking
Heat Aging Test: 168h/158°C
Minimum Tensile Strength At Heat Aging: 12 MPa
Elongation At Heat Aging: 200 %
Behaviour At Low Temperature: not cracking

UL 224

UL 224

Dielectric Strength: 24 kV/mm
Tensile Strength: 14 MPa
Elongation at break: 600%
Water Absorption: 0.2 %
Specifications: CSA, UL 224 125 °C 600V VW-1

IEC 60243

ASTM D2671

ASTM D2671



We assume no responsibility that the Product will be used for the intended purpose, this is beyond our control. It's up to the customer to check the suitability for a specific application by means of tests. Technical changes and errors reserved