

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0151360303](#)
Status: **Active**
Overview: MicroClasp™ Wire-to-Board System
Description: MicroClasp™-to-MicroClasp™ Off-the-Shelf (OTS) Cable Assembly, Single Row, 300.00mm Length, 3 Circuits, White

Documents:
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	15136
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MicroClasp™-to-MicroClasp™
Overview	MicroClasp™ Wire-to-Board System
Product Literature Order No	987651-6143
Product Name	MicroClasp™ OTS
UPC	191128149860
Physical	
Cable Length	300.00mm
Circuits (Loaded)	3
Color - Resin	White
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	4.631/g
Packaging Type	Bag
Pitch - Mating Interface	2.00mm
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.28mm
Wire Size AWG	22
Wire/Cable Type	UL 1061
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V AC (RMS)/DC

Material Info

Reference - Drawing Numbers
Sales Drawing 2012341706-000



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per -ED/01/2017 (12 January 2017) Halogen-Free Status Not Low-Halogen	China RoHS
--	-------------------

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[15136](#) Series

Mates With
[55932](#) Vertical Header, [55935](#) Right Angle Header

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION