

PSEN 1.2-20 / 1 actuator

515120

Actuator for magnetic safety switch, cylindrical design M30, IP67, operating distance depending on the actuator 8/12 mm, height design 13 mm, PU = 1 actuator.



Technical details

General data	
Approval:	CE, UKCA, cULus Listed, EAC (Eurasian), TÜV
unit type:	Actuator
Technical data	
Environmental data	
ATEX category:	II 3GD EEx nC IIC T6
Ambient temperature:	-25 - 70 °C
Max. ambient temp. at 2000 m:	+70 °C
Perm. operating height ASL:	4000 m
Vibration to standard:	EN 60947-5-2
Acc. shock to standard1:	30g
Pollution degree clear.&creep.:	3
Mechanical data	
Housing material upper part:	PBT
Depth dimension:	16 mm
Net weight:	20 g
Gross weight:	21 g
Environment	
RoHS directive:	2011/65/EU, 2015/863/EU
RoHS conformity:	yes

RoHS exceptions:	no
REACH compliance:	Contains no SVHC substances
WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
Harmonized System Code:	85389099
UNSPSC 25:	39122205
EAN-Code:	4046548003376
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27274002
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC001487
Volume:	0 dm3