





Revision level		Revision Record	Changed	Date	Approved	Date
part	drawing					
—	01					
		See ECN 03793	A.A.C.	04/18/03	K.A.C.	04/30/03

SEE CHART	Group Unique Numbers	Product Code	Cable Range (mm)	Material	A	B	D	E	G	H	J	K	Min Loop Tensile Strength (newtons)	
	-	IT18FL_	1.5 to 19	PA66	1.0 ±0.2	2.5±0.2	3.8 ±0.5	4.5 ±0.5	110.0 ±5.0	5.0 ±0.5	20.5 ±0.5	9.0 ±0.5	80	
	-	IT18FL_VO		PA66VO										
Material														
Dimension tolerances unless otherwise specified .XXXX = .XXX = .XX = .X = NOTED ∠ =	ACAD 2004				Drawn G. GEIGER 10/09/91		Scale 2:1			Computer File Number CT\CST\2018007_01				
					Approved K.A.C. 04/30/03		Title IT18FL IDENTIFICATION TIE							
Dimension Units mm	ALL PROPRIETARY RIGHTS IN THE SUBJECT MATTER SHOWN ON THIS DRAWING ARE EXCLUSIVE PROPERTY OF HELLERMANNTYTON				HellermannTyton® 7930 N. Faulkner Rd. Milwaukee, WI 53224 Ph: (414) 355-1130 Fx: (414) 362-8338			Drawing—No					Format	
PERFORMANCE SPECIFICATION								CT2018007CST					AH	
Sheet 1 of 1														