


DESCRIPTION CONTROL			
REV	DRAW	DATE	APP



PIN ASSIGNMENT

P1	P2
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9
10	10
11	11
12	12
13	13
14	14
15	15
16	16
17	17
18	18
19	19
20	20
21	21
22	22
23	23
24	24
C1	C1
C2	C2
C3	C3
C4	C4
C5	C5
S	S

*	390	CARTON:46*30*25CM	1/400	PCS
*	390	PE BAG:30*28*0.08MM	1/400	PCS
*	390	PE BAG:10*12*0.06MM	1/50	PCS
*	390	PE BAG:3.5*3.5*0.06MM	1	PCS
10	370	NUTS:4.75*8.5*4.85MM(4-40UNC)(NICKEL PLATED)	2	PCS
9	370	HI TEAMP TAPE:W:35MM;L:120MM	1	PCS
8	370	FOIL-CU-41*85MM	1	PCS
7	370	PVC-BK10/50	19	G
6	370	PE-5321	10.5	G
5	370	SRW-14.7*22.6MM(4-40UNC)(NICKEL PLATED)	2	PCS
4	220	DVI-24P+4+KEY-FEMALE (WHITE INSULATION)(NICKEL PLATED SHELL) (PIN GOLD FLASH)(BACK-NUTS)(4-40UNC)	1	PCS
3	220	DVI-24P+4+KEY-MALE (BLACK INSULATION)(NICKEL PLATED) (PIN GOLD FLASH)	1	PCS
2	220	SOL-WIRE-63/37-1.0	1.5	G
1	210	JUMP WIRE-28-1007-2*40*2MM	30	PCS
NO	PART NO	DESCRIPTION	QTY	UNIT

RoHS COMPLIANT



OUTER MOLDING	GC.DVI/HD15 076		
INNER MOLDING	GC.DVI/HD15 077		
		ITEM: 489343	REV R
DRAW, BY: 鍾有涓		SCALE: NONE	DATE: 2007-12-02
CHECK, BY:		CUSTOMER: C331<RS>	
APP, BY:		CUSTOMER P/N:	
ALL DIMENSIONS IN mm			