

FEATURES

- **Sintered Bronze Material:** Provides high wear resistance and durability.
- **Flanged Design:** Ensures secure positioning and easy installation.
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with moderate dynamic loads.
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads.
- **Bore Size of 15.02 mm:** Fits standard shaft sizes for versatility.
- **Outside Diameter of 19.05 mm:** Compact size for space-constrained applications.
- **Width of 20 mm:** Offers stability and support.

RS PRO 15.02 mm Flanged Plain Bearing

RS Stock No: 529-029



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flanged plain bearing is designed for applications requiring reliable and efficient motion control. Made from sintered bronze, it offers excellent durability and performance in various industrial settings. The bearing's flanged design ensures secure positioning and ease of installation, making it ideal for use in machinery and equipment where space is limited.

General Specifications

Bore Size	15.02 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	19.05 mm
Width	20 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

