



Fluted Anti-Fatigue Takes the sting out of standing

- Durable anti-fatigue mat with robust fluted PVC surface.
- Ribbed surface helps to provide a firmer footing.
- 'Cushion' foam backing provides good levels of comfort underfoot.
- Ramped edges reduce the risk of tripping and allow easy trolley access.
- Available as single workstation mats or in rolls.



Technical Specification

Material:	Vinyl top surface with PVC foam backing (fusion bonded, not glued)
Surface Finish:	3mm fluted ribbed embossed surface
Product Height:	10mm
Roll Length:	15.3m
Operating Temperature:	0°C to +60°C
Resistant to Chemicals:	The upper surface of the PVC provides limited resistance to chemicals and oils
Environmental Resistance:	Suitable for dry indoor environments
Typical Applications:	Packing stations, assembly areas, production lines where regular turning occurs
Installation Method:	Loose lay
Cleaning Method:	Brush/Mop the top surface
Country of Origin:	China

Sizes	Black	Weight
0.6m x 0.9m	FA010001	4.15 kg
0.9m x 1.5m	FA010002	10.38 kg
0.9m x 3m	FA010003	20.76 kg
0.9m x 15.3m	FA010004	105.80 kg
0.9m x per linear metre	FA010004C	6.91 kg