

Han Compact - GS - M25



Part number	19 12 008 0526
Specification	Han Compact - GS - M25
HARTING eCatalogue	https://b2b.harting.com/19120080526

Identification

Category	Hoods/Housings
Series of hoods/housings	Han-Compact [®]
Type of hood/housing	Hood
Description of hood/housing	for standard cable gland With separate PE terminating point for all inserts of size Han-Compact®

Version

Locking type	Single locking lever
Size	Han-Compact [®]
Version	Side entry
Cable entry	1x M25
Field of application	Hoods/housings for industrial applications

Technical characteristics

Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4
	12

Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
RoHS	compliant

Page 1 / 2 | Creation date 2019-11-14 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electric GmbH & Co. KG | Wilhelm-Harting-Straße 1 | 32339 Espelkamp | Germany
Phone +49 5772 47-97100 | electric@HARTING.com | www.HARTING.com



Material properties

ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

Specifications and approvals

Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076 UL 2237 PVVA2.E318390 CSA-C22.2 No. 182.3 ECBT8.E235076 CSA-C22.2 No. 182.3 PVVA8.E318390

Commercial data

Packaging size	1
Net weight	305 g
Country of origin	Germany
European customs tariff number	85389099
eCl@ss	27440202 Shell for industrial connectors