

Rittal – The System.

Faster – better – everywhere.

Slide rails, depth-variable for TS IT, TE – DK 5501.480

Date : Nov 21, 2017

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Slide rails, depth-variable for TS IT, TE – DK 5501.480

created: 21.11.2017 on www.rittal.com/com-en



Product description

Benefits:	Tool-free, time-saving one-man assembly from the enclosure front All three mounting holes in the EIA system punchings are available for screw-fastening the equipment. Alternatively, direct screw fastening to the 482.6 mm (19") system punchings is also possible
------------------	--

Applications:	For mounting between the front and the rear pair of mounting angles To support heavy installed equipment To adapt to individual distances between 482.6 mm (19") levels
----------------------	---

Material:	Sheet steel
------------------	-------------

Surface finish:	Zinc-plated
------------------------	-------------

Supply includes:	Assembly parts
-------------------------	----------------

Note:	Effective contact surface 25 mm per side
--------------	--

Product features

To fit:	Enclosure type: TS IT Enclosure type: TE 7000
----------------	--

Installation options:	482.6 mm (19") L mounting angles, front and rear 482.6 mm (19") mounting frames front and rear
------------------------------	---

Distance between levels:	min.: 600 mm max.: 900 mm
---------------------------------	------------------------------

Contact surface:	Width: 25 mm
-------------------------	--------------

Load capacity:	150 kg
Packs of:	2 pc(s).
Weight/pack:	3.75 kg
EAN:	4028177679030
Customs tariff number:	73269098
ETIM 6.0:	EC002620
ETIM 5.0:	EC002620
eCl@ss 8.0/8.1:	27189261
eCl@ss 7.0/7.1:	27182590
eCl@ss 6.0/6.1:	27182590
eCl@ss 5.1/5.1.4:	27182504
Product description (long):	DK Slide rail, support surface Width: 25 mm, depth-variable, 150 kg, For two 482.6 mm (19") attachment level (front+rear), distance between levels:: 600-900 mm