



Main

Range	Mureva Styl
Range of product	Mureva Styl
Product or component type	Socket-outlet
Device presentation	Complete product
Outlet poles configuration	2P + E
Outlet standard description	Pin earth
Outlet standard deviation	French
Colour tint	White (RAL 9003)

Complementary

Device mounting	Surface
Socket number	2
Rated current	16 A
[Ue] rated operational voltage	250 V AC
Condition of use	Indoor/outdoor
Fixing mode	By screws
Height	76 mm
Width	147 mm
Depth	64 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
Outlet standard	CEE 7/5

Environment

IP degree of protection	IP55
-------------------------	------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant with Exemptions
Mercury free	Yes
Sustainable packaging	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations