

**CAB CAB PC 203018 G**



**Order symbol:** CAB PC 203018 G  
**Product nbr:** 8113331  
**Description:** Cabinet, PC, Grey door  
**Remarks:** Latch on the short side

**EAN:** 6418074020024  
**EI. number:**  
 Finland: 3424103  
 Electric No. 8212020401  
 Denmark:  
 Electric No. Italy: 7821010  
 Electric No. Sweden: 2539963

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Sample photo

Dimensions:		Length	Width	Height	Accessories:		
mm:		300	200	180	EKIV 17	DIN-35 Mounting rail	
inch:		11.8	7.9	7.1	DS35170E1	DIN-35 Mounting rail	
<b>Materials:</b>						EKIV 27	DIN-35 Mounting rail
<b>Material:</b>		Polycarbonate			DS35270E1	DIN-35 Mounting rail	
<b>Base colour:</b>		RAL 7035 -light grey			FP A 23	Swing-out door/Front plate	
<b>Cover colour:</b>		RAL 7035 -light grey			MB 12225 AL	Swing door set	
<b>Gasket material:</b>		Polyurethane			FP 23	Front plate	
<b>Temperatures:</b>						FP 12-23	Front plate
<b>Temperature °C (short term):</b>		-40 ... 120 °C			DRF 23	DIN rail frame set	
<b>Temperature °C (continuous):</b>		-40 ... 80 °C		<b>Rating:</b>			
<b>Temperature °F (short term):</b>		-40 ... 250 °F		Ingress Protection (EN 60529): IP65			
<b>Temperature °F (continuous):</b>		-40 ... 175 °F		Impact Resistance (EN 62262): IK08			
<b>Accessories:</b>						Electrical insulation: Totally insulated	
EKIV 23		Mounting plate				Halogen free (DIN/VDE 0472, Part 815): 1	
						UV resistance: UL 508	
						Flammability Rating: UL 746C 5"	
						Glow Wire Test (IEC 695-2-1) °C: 960	
						<b>Certificates:</b>	
						Germanischer Lloyd (GL)	
						SGS Fimko	
						Lloyds Register of Shipping (LR)	
						Gost R	

