

FEATURES

- 2 contacts
- Pitch of 5 mm
- Single row
- Pluggable
- Through hole mounting
- Female
- Screw termination method
- Straight body orientation
- Made of PBT polyamide (grey)
- Voltage Rating of 300 V
- Current Rating of 10
- Dimensions of 10.8 mm (width) x 10.7 mm (length) 13.5 mm (depth)
- Operating temperature range of -40°C to +105°C

RS PRO 5mm Pitch, 2 Way PCB Terminal Strip

RS Stock No.: 494-8849



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

PCB Terminal Block



Product Description

This 4-way PCB (printed circuit board) terminal strip is used in conjunction with PCB header strips. It allows you to link up wires across different PCBs quickly and easily.

General Specifications

Number Of Contact	2
Number Of Rows	1
Mounting Type	Through Hole
Gender	Female
Termination Method	Screw
Туре	Plug
Body Orientation	Straight
Colour	Grey
Material	PBT
Flammability Rating	UL 94 V-0
Applications	PCB

Electrical Specifications

Current Rating	10A
Voltage Rating	300V
Insulation Resistance	1000mΩ
Insulation Withstand Voltage	1500V ac



Mechanical Specifications

Pitch	5mm
Depth	13.5mm
Width	10.8mm
Length	10.7mm
American Wire Gauge	14AWG to 20AWG

Operation Environment Specifications

Operating Temperature Range	-40°C to 105°C

Approvals

Compliance/Certifications	EN61340
---------------------------	---------



