
push-in connector NPQP-D-Q6-E-FD-P10 Part number: 133092

Part number: 133092





Data sheet

Feature	Value
Size	Standard
Nominal size	4 mm
Container size	10
Design structure	Push/pull principle
Temperature dependent operating pressure	-0.95 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	4 - Very high corrosion stress
Food-safe	See Supplementary material information
Ambient temperature	-20 60 °C
Product weight	5.5 g
Pneumatic connection, port 1	for tubing, 6mm outside diameter
Pneumatic connection, port 2	For tubing outside diameter 6 mm
Materials note	Contains PWIS substances
	Conforms to RoHS
Material housing	PP
Material of tube retaining claw	High alloy steel, non-corrosive