



PRODUCT-DETAILS

E 91N/32s

Fuse switch disconnecter



概要信息	
产品型号	E 91N/32s
产品ID	2CSM251503R1801
欧洲商品编号(EAN)	8012542515036
目录说明	Fuse switch disconnecter
详细描述	E 91N/32s is a fuseholder for overcurrent and short circuit protection with blown fuse indicator.

技术参数	
标准	IEC 60947-3
额定电压 (U _r)	acc. To IEC 400 V acc. To UL 690 V
额定工作电压	AC-20B 690 V AC-22B 400 V
额定绝缘电压 (U _i)	1 kV
辅助电压AC/ DC	LED Indicator 24-1000 V
额定频率 (f)	50/60 Hz
功率损耗	at Rated Operating Conditions per Pole 3 W

保护极数	1
极数	2P
中性端子位置	Right
拧紧力矩	2...2.5 N·m
利用类别	Connecting and disconnecting under no-load conditions - occasional actuation (AC-20B) Switching of mixed resistive and inductive loads, including moderate overloads - occasional actuation (AC-22B)
Lock Type	Padlockable when open
安装类型	DIN-Rail
封口类型	Sealing Wire
Material of Conductor	Copper
提供的选项	With LED
推荐的螺丝刀	Pozidriv 2
Shock and Vibration Withstand acc. to IEC 61373	Category 1, Class B
连接容量	Rigid 2x5 mm ² Stranded 2x2-5 mm ²
熔断器规格	10x38 mm max. 90% with temp. +20 °C 50% with max. temp. +40 °C
额定工作电流AC (I _e)	32 A

Material Compliance

RoHS信息	9AKK106713A5623
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS日期	1/1/2014
REACH Declaration	9AKK108467A9482
REACH Information	True - contains substances > 0.1 mass percentage
REACH Date	20240429
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363

环境条件

周围环境温度	Operation -5...+40 °C Storage -25...+70 °C
防护等级	IP20
允许的最高工作海拔	2000 m
耐振动符合IEC 60068-2-6标准	1 mm 2 ... 13 Hz
抗机械冲击符合IEC 60068-2-27标准	15g 18 shocks 13 ms
环境信息	See RoHS Information

UL/CSA适用的技术参数

连接容量UL/CSA	Rigid 2x10 AWG Stranded 2x14-10 AWG
------------	--

尺寸

宽度(模块化垫片数)	2
产品净宽	35 mm
产品净高	85 mm
产品净深	64 mm
产品净重	131 g
内深 (t ₂)	64 mm

订货信息

1级包装单元	box 3 piece
1级包装 总重	0.396 kg

认证及声明（文件编码）

BV认证	9AKK108467A0330
CCC认证	9AKK108467A0340
符合性声明 - CE	9AKK106713A5623
IMQ认证	9AKK108467A0324
KRS认证	9AKK108467A0337
LR认证	9AKK107991A7313
UL认证	9AKK107992A1039
认证机构	IMQ, BV, Korean register, CCC, EAC, UL

Installation

说明书和手册	No document needed
--------	--------------------

Popular Downloads

数据手册，技术资料	2CSC444002B0204
-----------	-----------------

分类

ETIM 8	EC002705 - Holder for cylindrical fuse
ETIM 9	EC002705 - Holder for cylindrical fuse
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer
CN8	85361050
e级	V11.0 : 27142121
对象分类代码	F

Accessories

Identifier	Description	Type	Quantity	Unit Of Measure
2CSM277333R1801	Fuse link	E 9F10 GG05	1	piece
2CSM277113R1801	Fuse link	E 9F10 GG1	1	piece
2CSM258723R1801	Fuse link	E 9F10 GG2	1	piece
2CSM257543R1801	Fuse link	E 9F10 GG4	1	piece
2CSM256363R1801	Fuse link	E 9F10 GG6	1	piece
2CSM258633R1801	Fuse link	E 9F10 GG8	1	piece
2CSM257453R1801	Fuse link	E 9F10 GG10	1	piece
2CSM256273R1801	Fuse link	E 9F10 GG12	1	piece
2CSM277543R1801	Fuse link	E 9F10 GG16	1	piece
2CSM277323R1801	Fuse link	E 9F10 GG20	1	piece
2CSM277103R1801	Fuse link	E 9F10 GG25	1	piece
2CSM258713R1801	Fuse link	E 9F10 GG32	1	piece
2CSM257473R1801	Fuse link	E 9F10 AM05	1	piece
2CSM256293R1801	Fuse link	E 9F10 AM1	1	piece
2CSM277563R1801	Fuse link	E 9F10 AM2	1	piece
2CSM277343R1801	Fuse link	E 9F10 AM4	1	piece
2CSM277123R1801	Fuse link	E 9F10 AM6	1	piece
2CSM258733R1801	Fuse link	E 9F10 AM8	1	piece
2CSM257553R1801	Fuse link	E 9F10 AM10	1	piece
2CSM256373R1801	Fuse link	E 9F10 AM12	1	piece
2CSM258643R1801	Fuse link	E 9F10 AM16	1	piece
2CSM257463R1801	Fuse link	E 9F10 AM20	1	piece
2CSM256283R1801	Fuse link	E 9F10 AM25	1	piece
2CSM277553R1801	Fuse link	E 9F10 AM32	1	piece
2CCS500900R0181	Spare parts	ZLS725	1	piece
2CCS400900R0091	Spare parts	ZLS726	1	piece

分类

低压产品及系统 → 线路保护产品 → Protection and Safety Devices → Cylindrical Fuse Holders and Fuse Switch Disconnectors

