

## Datasheet

# 6 Piece Impact Screwdriver Set

RS Stock number [541-6539](#)



### Specification:

- Material: Chrome vanadium steel for impact driver and bit coupler, chrome molybdenum steel (s-2) for screwdriver bits, P.P injection grip
- Finish: Satin chrome plated for impact driver, bit coupler and sandblast bits
- Hardness: Heat treated to HRC: 35 ~ 54 for impact driver & bit coupler, HRC: 56 ~ 62 for screwdriver bits

### Contents:

1 pc-1/2" DR. reversible impact driver with black colour finger guide shock-absorbing injection grip (affixed with RS poly label)  
1 pc-1/2" dr. to 5/16" hexagon bit coupler (steel sheet with pin ball type)  
4 pc-35 mm (5/16") impact driver bits: parallel slotted: 9 mm Phillips: no.2, no.3 and no.4  
2 pc-80 mm (5/16") impact driver bits: Phillips: no.2, no.3  
Injection case sizes:8" (w) x 3" (d) x 2-3/4" (h)

### Remarks:

Torque load & go-no gauges of bits meet din 8764 & 5264 standard & impact driver portion meet din3120 standards.