



Product data sheet

Power tools for trade & industry

Cordless Wood Stapler

GTH 18V-38 M



Cordless and gasless narrow crown stapler with pneumatic performance and bump fire mode

The most important data

Staple length	10 – 38 mm
Staple width	5.8 mm
Triggering system	Full sequential actuation + contact actuation with automatic reversion

Part Number 0 601 482 501

Technical data

Technical data

Collation angle	0 °
Nail/Staple type	Narrow crown staple
Triggering system	Full sequential actuation + contact actuation with automatic reversion
Weight excl. battery	3.05 kg
Battery voltage	18.0 V
Magazine capacity	110 Pcs
Packaging dimensions (width x length x height)	360 x 444 x 254 mm
Compatible nails/staples	Bosch staples, Other
BITURBO	No
Staple width	5.8 mm
Staple length	10 – 38 mm

Noise/vibration information

Total vibration values

Vibration emission value ah	1.9 m/s ²
Uncertainty K	1.5 m/s ²

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Cordless freedom with the power of a pneumatic stapler – without compressors, gas cartridges, or cords
- Activate and operate the tool with just one hand thanks to the thumb-actuated power switch
- Gentle on your wrist and lungs thanks to very low recoil and gasless operation

