



Specification

VI13800 Voltage Indicator



Electrical

Nominal voltage range: 50 - 600V DC/AC rms

Nominal voltage threshold indications:

50, 100, 200, 400 V DC/AC rms

Voltage threshold tolerance:

Conforms to BS EN 61243-3:2010

Polarity & voltage indication: $\geq 12V$ DC/AC rms

AC/DC voltage detection: automatic

Range detection: automatic

Response time: $< 0.1s$

Frequency range: DC, 1 - 400Hz

Test current: $< 3.5mA$ at 600V DC/AC rms

Duty ratio: 30s ON (operated) / 240s OFF (recovery)

Environmental

Temperature & Humidity (Operating & Storage): $-10^{\circ}C$ to $55^{\circ}C \leq 85\%$ R.H.

Altitude: up to 2000m

General

Power: From circuit under test

Dimensions: 205(L) x 67(W) x 27(D) mm

Weight: 130g approx.

Includes: Instructions

Safety

Conforms to BS EN 61243-3:2010 CAT IV 600 V, CAT III 1000V

Class II, Double Insulation

Pollution Degree 2

IP rating: IP54

EMC

Conforms to BS EN 61326-1

Check out what else you can get from Martindale:

- 17th Edition Testers
- Accessories
- Calibration Equipment
- Continuity Testers
- Electricians' Kits
- Environmental Products
- Full Calibration & Repair Service
- Fuse Finders
- Digital Clamp Meters
- Digital Multimeters
- Labels
- Microwave Leakage Detectors
- Motor Maintenance Equipment
- Multifunction Testers
- Non-trip Loop Testers
- Pat Testers & Accessories
- Phase Rotation Testers
- Proving Units
- Socket Testers
- Thermometers & Probes
- Test Leads
- Voltage Indicators
- Specialist Metrohm Testers (4 & 5kV)
- Specialist Drummond Testers



Martindale Electric Company Limited
Metrohm House, Penfold Trading Estate, Imperial Way, Watford WD24 4YY, UK
Tel: +44(0)1923 441717 Fax: +44 (0)1923 446900
E-mail: sales@martindale-electric.co.uk
Website: www.martindale-electric.co.uk

© 2013 Martindale Electric Company Ltd.
Registered in England No. 3387451. E. & O.E. LIT13800 Document Rev2