



Product data sheet

Power tools for trade & industry

Cordless Ratchet Wrench

PRO GRC 12V-60 1/2 SN



Compact ratchet wrench handles screws in tight spaces with ease

The most important data

Battery voltage	12.0 V
Torque, max.	60 Nm

Part Number 0 601 9N8 500

Technical data

Technical data

Weight excl. battery	0.78 kg
Torque, max.	60 Nm
Battery voltage	12.0 V
Packaging dimensions (width x length x height)	208 x 340 x 98 mm
Torque, max. (hard screwdriving applications)	60 Nm
Weight incl. battery	1.16 kg
BITURBO	No

**BOSCH**

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Outstanding tool control and comfortable grip thanks to ergonomic design and small circumference Compact and convenient with lean 12 V system for accessing tight spaces and LED light to illuminate dark areas Efficient, intuitive operation thanks to variable speed trigger Robust and durable thanks to metal housing



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

