

Roof outlet filter, Extract: W: 345 mm, H: 265 mm, RAL 7035, IP54,



Model		
product brand name		SIVACON
product designation		outlet filter for roof mounting
type of ventilation		ventilation
fan design withdrawable fan		No
design of the product EMC version		No
General technical data		
cutout width		345 mm
cutout height		265 mm
Protection class		
protection class IP		IP44
Appearance		
color		light grey
Product details		
product component fan		No
Mechanical Design		
height		340 mm
width		420 mm
depth		83 mm
installation location		Control cabinet roof
fastening method		screw fixing
fastening method		
• 19-inch installation		No
• wall mounting		No
net weight		4.5 kg
material		metal
ambient temperature during operation		
• minimum		-10 °C
• maximum		55 °C
Approvals Certificates		
General Product Approval		other
		Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6000-5DE40>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6000-5DE40>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6000-5DE40

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

