

ROLL.6M4A

Roller cabinet 6 drawers, 759 x 421 mm, 4 modules per drawer

- 6 drawers roller cabinet = 20 modules
- 3 drawers height 60 mm = 12 modules
- 2 drawers height 130 mm = 8 modules

[View more features](#)



Additional Features

- 1 drawer height: 200 mm, can also be fitted with modules
- Drawers can be fitted with thermoshaped or foam modules from FACOM Modular system program
- Drawers useful dimensions: L 759 x D 421 x H 60/130/200 mm
- Load resistance per drawer: 20/25/30 kg
- Worktop: Large worktop (760 x 460 mm) made of polypropylene with fiber impact and chemical resistant, static load resistance 900 kg
- Even more functional: Integrated bi-material handle with soft grip on each side of the trolley. One for moving and one for lifting the trolley over obstacles
- Dedicated slots for 3 screwdrivers
- Ergonomic and secure drawers: Polypropylene drawer handles with safety hooks. No risk of opening while in motion
- Central locking system with key lock, supplied with 2 keys, 1 of which is hinged
- Manoeuvrability: Low starting effort, long life, high resistance to heavy loads
- 4 wheels diameter 125 mm, 2 fixed and 2 swivel, each equipped with a brake for more stability when working at a standstill
- Roller cabinet delivered with wheels already attached
- Accessories: Supplied with 1 bottle holder, fits on the right or left
- Sides are perforated to receive some JET accessories
- Additional partitions can be purchased as an option if required: JET2.15 for 60 mm drawers and JET2.16 for 130 mm drawers

Specifications

Drawer Separators	Yes
Material of Drawer Corner Protectors	Soft Plastic
Locking System	Central
Wheel Diameter	125 mm
Worktop with Integrated Handles	Yes
Type of Side Handle	Plastic
Possibility of Accessorization	Yes
Color	Red 3020
Material of Box Corner Protectors	Soft Plastic
Worksurface Can Receive a Vice	No
Number of Handles	1
Wheels with Brake	Yes
Tilting Handle	No
360' Rotation Capacity	Yes
Additional Top Chest Can be Added	No
Maximum Worktop Load	900 Kg
Drawer Depth	421 mm
Number of Drawers	6
Drawer Height	60/130/200 mm
Drawer Mat	No
Number of Swiveling Wheels without Brake	1
Product Height	972 mm
Product Weight	68 Kg
Number of Fixed Wheels with Brake	2
Number of Drawer Separators	20

Product Handle Type	Plastic
Number of Wheels	4
Slides Material	Metal
Drawer Capacity	30 Kg
Drawer Length	759 mm
Number of Fixed Wheels without Brake	1
Self-Closing Slides	No
Type of Lock	Key
Available Accessories	Bottle Holder
100% Opening of Drawers	Yes
Body Metal Thickness	1 mm
Product Length	969 mm
Surface Treatment	Plasticized
Static Overall Weight Capacity	900 Kg
Secure Closing System - Safety Hook	Yes
Worktop Material	Plastic
Worksurface Can Receive Accessories	No
Anti-tip System - One Drawer At A Time	No