




Technical data

51306

One direction thrust ball bearings



VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	30 mm
D - External diameter	60 mm
T - Thrust bearing height	21 mm
rs - Min fillet radius	1 mm
Mass	0,269 kg

PRODUCT PERFORMANCE

Ca - Dynamic axial load rating	43000000 mN
C0a - Static axial load rating	78500000 mN
Cua - Limit axial load rating	3550000 mN
N lim - Oil lubrication limit speed	23400 °/s
N lim - Grease lubrication limit speed	16800 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

Da max - Max shoulder diameter OR	42 mm
da min - Min shoulder diameter IR	48 mm

