



## Calinor Polycarbonate Floodlight PIR Cool White 10W Black



- Compact and economic polycarbonate LED floodlight suitable for semi commercial applications
- Polished faceted reflector and textured glass for optimum performance
- Pre-wired with 1 metre of rubber insulated cable for ease of installation (500mm for 10W)
- Polycarbonate spike accessory allowing installation into lawn and garden applications
- PIR versions complete with manual override facility
- Non-dimmable

### General Information

Lamp Type	LED
IP Rating	IP65
IK Rating	IK08
Class Protection	2
Internal / External	Internal / External
Surface / Recessed / Suspended	Surface
Warranty (Years)	2
Material	Polycarbonate



#### Technical Information

Wattage	10W
Lumens Delivered	940lm
Lm/W	94lm/W
Beam Angle	75/90
CRI	80
CCT	4000K
Input	220/240V
Hertz	50/60Hz
Operating Temp	-15°C to 40°C
Lumen Depreciation	L70 51,000h
Power Factor	0.5

