



**Detectable**  
**T&B Catalog Number:**

TY527M-PDT

**UPC Number:**

78621099538

**Status:**

Active

**Description:**

Detectable Cable Tie, Bright Blue Polypropylene for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 334.57mm (13.172 Inches), Width of 6.86mm (0.27 Inches), Thickness of 1.52mm (0.06 Inches), Tensile Strength Rating of 267 Newtons (60 Pounds)

**Features**

Detectable by metal detectors, X-ray equipment, or visual detection.

Stainless Steel locking device.

**General**

Material Polypropylene

Color Blue

**Dimension Information**

Nominal Length (inches) 13

Length (inches) 13.40

Width (inches) .27

Max. Wire Bundle Diameter (inches) 3.5

**Specifications**

Temperature Rating -40°F to 185°F

Flammability Rating UL 94 V-2

**Tooling**

Application Tools ERG120

**Packaging**

T&B Order Multiple 50

T&B Inner Pack 50

Package in Units 500

Package Type Regular

T&B Sold in UOM Each

T&B Weight Per UOM 5 lbs. per 1000

**Application Support**

MSDS Number sds-00046-tb2

T&B Sales Drawings wsd-000276

Material Selection Guide Available on Website

Test Report Available on Website

**Certifications**

RoHS Compliance Yes

Ty-Rap Certifications Ty-Rap Detectable Cable Ties are a safety and contamination solution for Food & Beverage processing plants and may aid companies in meeting the U.S. Food and Drug Administration (FDA) Hazard Analysis and Critical Control Points (HACCP) safety standards and the European Union (EU) hygiene monitoring regulations.

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)