


# rotary push-in fitting

## QSR-1/8-6

Part number: 153402

FESTO

360° rotatable, with ball bearing, male thread with external hexagon.



## Data sheet

Feature	Value
Size	Standard
Nominal size	3.4 mm
Type of seal on screw-in stud	coating
Assembly position	Any
Container size	1
Design structure	Push/pull principle
Operating pressure complete temperature range	-0.95 ... 6 bar
Temperature dependent operating pressure	-0.95 ... 14 bar
Max. speed	500 1/min
Maritime classification	see certificate
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	0 ... 60 °C
Max. tightening torque	7 Nm
Max. radial moment	0.012 Nm
Product weight	18 g
Pneumatic connection, port 1	Male thread R1/8
Pneumatic connection, port 2	For tubing outside diameter 6 mm
Colour of release ring	blue
Materials note	Conforms to RoHS
Material housing	PBT
Material release ring	POM
Material of tubing seal	NBR
Material of tube retaining claw	High alloy steel, non-corrosive