


Features

- Flexible and durable SVT3X18AWG- pvc cable
- USA /CANADA NEMA5/15 Plug
- Moulded IEC -C13 Connector
- Fully moulded connectors for strength and durability
- Integrated strain relief for connection support and protection

RS PRO 2.00m Power cable C13, IEC to NEMA 5/15 10A 125V

RS Stock No: 0771781



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- From RS PRO a high quality and durable power cord for connecting an appliance to a mains power supply. This power cord is fully equipped UL/CSA approved N5/15P on one end and an IEC C13 type connector on the end that connects to the appliance. The power lead features integrated strain relief that provide additional protection and support to the connector, Power cord rating is 10A/125V.

General Specifications

Connector A	C13, IEC Female – Straight EN60320 /C13
Connector B	NEMA 5/15 Straight 498G UL/CSA
Sheath Colour	Black
Insulation	Green, White, Black
Material	PVC
Applications	DIY and home improvements, maintenance work. Household entertainment (tv's, satellite boxes, routers). Home Appliances, monitors, computers, phones any electrical item that needs mains power.

Mechanical Specifications

Length	2.00m
--------	-------

Electrical Specifications

Power Cord Rating	10 A - 125V
Visual Inspection	100%
Electrical Test	100%
High pot test wire to wire	3k Vac for 2 sec.
Continuity test	25Aac to grounding / 20Aac to line and neutral
Polarity test	yes
Skin high pot test	6k Vac line to skin

Protection Category

Environmental Conformity	Eu-Directive 2002/96/EC (WEEE)
	Eu-Directive 2003/11/EC (Council Directive 76/769/EEC)
	Eu-Directive 2002/95/EC (RoHS-Compliant)

Approvals

C13 CONNECTOR	UL / CSA
NEMA5/15 P	UL / CSA
Cable	CE /UL / CSA

All dimensions in mm

