

Features

- S012.101 fitted with a 3D Flex system allowing to work, even when tilted upside down. Thanks to this solution, you can reach the most inaccessible areas with unprecedented ease.
- High-pressure tank
- Hi-Vis bright green colour for easy localisation in a workshop

RS PRO Pressure Sprayers BASIC Line

RS Stock No.: 0708700, 0708701, 0708702, 0708703



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Basic Pressure Sprayers with capacities from 1.5 litres up to 12 litres.

The RS PRO sprayers are characterised by exceptional quality and attention to detail. All Basic Line pressure sprayers have a pressure of 4 bar, which makes spraying easier and the pressure more stable. All tanks have a 5-year warranty.

- The 1.5 litres sprayer (0708700), comes with a 3D-flex system, adjustable nozzle and very ergonomic smart bottle shape and dosing valve lock.
- The 5, 9 and 12 litres sprayers (0708701, 0708702, 0708703) come with a lance with jet regulation, dosing valve lock, three-layer reinforced hose and efficient high-pressure pump.

Technical specification:

Stock No.	Sprayer Type	Capacity (L)	For Use With	Colour	Working Pressure (bar)
0708700	Handheld	1.5	Neutral Products / Pesticides	Green	4
0708701	Handheld / Shoulder	5	Neutral Products / Pesticides	Green	4
0708702	Handheld / Shoulder	9	Neutral Products / Pesticides	Green	4
0708703	Handheld / Shoulder	12	Neutral Products / Pesticides	Green	4

Similar products:

Acid-Proof Pressure Sprayers

Stock No.	Sprayer Type	Capacity (L)	For Use With	Colour	Working Pressure (bar)
0708691	Handheld	1.5	Acids	White	4
0708692	Handheld / Shoulder	5	Acids	White	4
0708693	Handheld / Shoulder	9	Acids	White	4
0708694	Handheld / Shoulder	12	Acids	White	4

Alkalis-Proof Pressure Sprayers

Stock No.	Sprayer Type	Capacity (L)	For Use With	Colour	Working Pressure (bar)
0708695	Handheld	1.5	Alkalis	White	4
0708696	Handheld / Shoulder	5	Alkalis	White	4
0708698	Handheld / Shoulder	9	Alkalis	White	4
0708699	Handheld / Shoulder	12	Alkalis	White	4