

FEATURES

- Half-wave bridge rectifier in 24 V and 28 V types
- 230 V ac types can be used on 130 V dc supplies
- Body colour coded
- 5 Colours available: Red, yellow, blue, green, white

RS PRO White Cluster LED Indicator, 24 V ac/dc, 25 x 10mm Mounting Hole Size, Ba9s Termination

RS Stock No.: 211-695



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

Brought to you by RS Pro, a range of high quality LED cluster indicators. Each model has three lamps that supply a high illumination area. As standard with an LED cluster, the low power consumption and longevity make them an excellent addition to applications. Using a convenient bayonet connection, these indicators are fast and easy to install. All models are highly reliable and excellent quality.

General Specifications

Light Output Colour	White
Lamp Type	Cluster LED
Termination Type	Ba9s
Туре	Panel Mount
Intensity	2070 x 3 mcd
Type Of Illumination	Fixed Light
LED Colour	White
Applications	Fixed to PCB circuit boards mounted; Switches; Pushbuttons; Used as vehicle indicators

Electrical Specifications

Voltage Rating	24V ac/dc
Current Rating	17 (dc) mA, 9 (dc) mA
Rectifier	Half wave
Voltage Tolerance	10%

Indicators



Mechanical Specifications

Mounting Hole Size	25 x 10mm
Length	25mm
Shape	Round
Lamp Size	10mm

Operation Environment Specifications	
Temperature Rating	-30°C to 60°C

Approvals	
Compliance/Certifications	EN61340

