

# FSTWIFITGV

## Wi-Fi Controlled IP66 Fused Spur

### Features & Benefits

- IP66 Weatherproof available for Android and IOS only
- Remote controlled from your phone via Wi-Fi and a data connection
- Can reduce running costs if unwanted programmes are cancelled
- Supports multiple devices
- Supports multiple users
- Auto mode, with permanent ON, permanent OFF and holiday modes
- Optional 1 and 2 hour boost
- Advance function
- Supports additional programme sets, for half terms, holidays and seasonal programmes
- 6 ON/OFF periods, with daily repeats positive ON/OFF status, with colour coded display automatic summer/winter changeover



### Technical Data

Operating Voltage	230V AC
Frequency	50Hz
Installation Type	Surface Mount
WLAN-Standard	802.11 b/g/n 2.4GHz
Earth Class Rating	Class II
Operating Temperature	0°C to 40°C

# Data sheet

## FSTWIFITGV

Safety / Weathersafe Vision Outdoor Power

Ingress Protection Rating	IP65
Setting Type	WIFI (App Based)
VPN Support	May Affect Pairing
Program Modes	24 Hour/7 Day, 1 Hour/2Hour Boost
Switch type	Double Pole
Standby Consumption	<0.5W
Number of Channels	1
Switch rating	13A Resistive, 1000W Incandescent/Halogen, 500W Fluorescent, 500W LED, 100W CFL
Shortest Switching Time	1 Minute
Programmable Slots	6 ON, 6 OFF
Permanent ON Facility	Yes (App Enabled or Power Button)
Multiple Unit Support	Yes (Multiple Devices On App)
Cable Entry(s)	Back Entry, Multiple M20 Knockouts (Top, Bottom, Left, Right)

## General

Weight (g)	488
Height (mm)	148
Width (mm)	108
Depth (mm)	75.5
Body Construction	Polycarbonate
Product Colour	Grey
Accessories (Included)	Fittings, 13A Fuse
EAN Number	5012483013861

# Data sheet

## FSTWIFITGV

Safety / Weathersafe Vision Outdoor Power

Guarantee Period

3 Years

### Line Diagrams

