

FEATURES

- **Sintered Bronze Material:** Provides high strength and wear resistance, ensuring long service life
- **Flanged Design:** Facilitates easy installation and secure fitment
- **Dynamic Load Rating of 14 N/mm²:** Suitable for applications with varying load conditions
- **Static Load Rating of 50 N/mm²:** Capable of handling high static loads effectively
- **32.03 mm Bore Size:** Compatible with a wide range of shafts

RS PRO 32.03 mm Flanged Plain Bearing

RS Stock No: 558-487



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The RS PRO 32.03 mm Flanged Plain Bearing is designed for applications requiring reliable and efficient rotational movement. Made from sintered bronze, this bearing offers excellent durability and performance in various industrial settings. Its flanged design ensures easy installation and secure positioning, making it ideal for both static and dynamic applications.

General Specifications

Bore Size	32.03 mm
Dynamic Load Rating	14 N/mm ²
Product Type	Plain Bearing
Static Load Rating	50 N/mm ²
Sub Type	Flanged

Mechanical Specifications

Material	Sintered Bronze
Outside Diameter	40.06 mm
Width	20 mm

Approvals

Standards/Approvals	ISO 2795, ISO 9001:2008, UKAS 001
---------------------	-----------------------------------

