

Hedge Trimmer Brushless LXT®

DUH506

18V, 500 mm, 4 000 min⁻¹

Model DUH506 is a 500mm (19-3/4") cordless hedge trimmer powered by 18V LXT® Li-Ion battery.

Lightweight design. Constant speed control. Anti-restart function. Brushless Motor.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Brushless Motor	✓
Strokes per Minute (SPM)	4000 min ⁻¹
Length Of Blade	500 mm
Max blade opening	20 mm
Tooth Spacing	30 mm
Continuous Use 18V / 6.0 Ah Battery	75 min
Sound Power Level (L _{WA})	88 dB(A)
Sound Pressure Level (L _{pA})	80 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Hedge Trimming	≤ 2,5 / ≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Hedge Trimming	1,5 m/s ²

User benefits

- Brushless maintenance-free and long-life motor
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Electric brake for maximum productivity and increased operator safety
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

Other

User manual

Parts drawing