




Technical data

51324

One direction thrust ball bearings



VISUAL (S)



PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	120 mm
D - External diameter	210 mm
T - Thrust bearing height	70 mm
rs - Min fillet radius	2,1 mm
Mass	10,8 kg

PRODUCT PERFORMANCE

Ca - Dynamic axial load rating	296000000 mN
C0a - Static axial load rating	805000000 mN
Cua - Limit axial load rating	28300000 mN
N lim - Oil lubrication limit speed	6600 °/s
N lim - Grease lubrication limit speed	4680 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

Da max - Max shoulder diameter OR	157 mm
da min - Min shoulder diameter IR	173 mm

