



Part Number : [2451320430](#)
Product Description : Micro-fit 3.0-to-Micro-Fit 3.0 Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 3.0m Length, 4 Circuits, Black
Series Number : 245132
Status : Active
Product Category : Power and Signal Cable Assemblies
Engineering Number : 795161043



Documents & Resources

Drawings
[2451320430_sd.pdf](#)
[245132043-PK.pdf](#)

3D Models and Design Files
[2451320430_stp.zip](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	245132
Description	Micro-fit 3.0-to-Micro-Fit 3.0 Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 3.0m Length, 4 Circuits, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Fit 3.0 Both Ends
Product Name	Micro-Fit 3.0
Type	Overmolded Assembly
UPC	889056862158

Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	300V AC

Physical

Cable Length	3.0m
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin

Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	159.132/g
Number of Rows	2
Overmolded	Yes
Packaging Type	Bag
Pitch - Mating Interface	3.00mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Single Ended	No
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 2464
Wire Size (AWG)	20

Mates With / Use With

Mates with Part(s)

Description	Part Number
Micro-Fit 3.0 Dual Row Plug Housings	<u>43020</u>
Micro-Fit 3.0 Dual Row Headers	<u>43045</u>
Micro-Fit 3.0 Dual Row Test Plugs	<u>44242</u>