

# LinkStation™ 210 series

## Network Attached Storage

**BUFFALO**™

LS210D-EU

## Fast, Easy, and Fan-less

Buffalo™ Technology's new LinkStation™ 210D series combines the convenience and capacity of Network Attached Storage with an incredibly easy User Interface and super-quiet fan-less operation.

The LS210 is fast and ready for intensive data storage tasks and can even be set up via Smartphones with a new mobile-optimised and intuitive interface.

Buffalo's new LinkStation™ can also stream up to 4 HD films simultaneously allowing each family member to watch their favourite film, on their own device, at the same time.

All of this is combined with a free personal private cloud for remote access from anywhere via apps for Tablets and Smart Phones or via web browsers: keeping all your data at your fingertips no matter where you are.

Buffalo™ Technology's LS210 series is a single bay Network Attached Storage available fully populated with 2 or 3TB capacity.



LS210D-EU

## Features and Benefits

- Single bay NAS available fully populated with 2 or 3TB capacity
- High-performance Dual Issue CPU
- Fan-less design for super-quiet operation
- Read speeds up to 100MB/s, write speeds up to 50MB/s
- Provides a central location – and sharing capability across your network – for growing media libraries including iTunes®
- Award-winning NovaBACKUP® for PC: 5 licenses included
- Data accessible from anywhere via Tablet or Smartphone apps or web browsers
- Share your printer among multiple users and devices
- Time Machine® ready for multi-client backups
- New easy-to-use Mobile-optimized interface



# LinkStation™ 210 series



## Network Attached Storage

LS210D-EU

## Specifications

System	
CPU	Marvell ARMADA 370, 800MHz Dual Issue
RAM	DDR3 256MB
Performance	Read: 100+MB/s, Write: 50+MB/s (Direct Gigabit Network Connection)
Internal Hard Drives	
HDD Interface	SATA
Capacities	2, 3TB
Number of Drives	1
Interfaces	
LAN	
Standard Compliance	IEEE802.3ab / IEEE802.3u / IEEE802.3 Standard
Connector Type	RJ-45
Number of Ports	1
Data Transfer Rates	10/100/1000Mbps
USB	
Standard Compliance	USB 2.0
Connector Type	USB type A
Number of Ports	1
Data Transfer Rates	480Mbps
Protocol Support	
Networking	TCP/IP
File Sharing	SMB/CIFS, FTP, HTTP/HTTPS, AFP
Management	HTTP/HTTPS
Time Synchronisation	NTP
Other	
Supported OS	Windows 8.1 (32/64-bit), Windows RT 8.1*, Windows 8, Windows® RT*, Windows® 7 (32/64-bit), Windows® Vista™ (32/64-bit), Windows® XP (32-bit), Mac OS® X 10.6 or later*, iOS5 or later*, Android 2.3 or later
Dimensions (WxDxH)	45x205x128mm
Weight	1.1kg
Operating Environment	5-35°C, 20-80% (non-condensing)
Power Consumption	Ave 16.5W / Max 24W (with no USB devices connected)
Power Supply	External, AC 100-240V, 50/60Hz

\*Some included optional utilities are not supported.

### Product Codes

LS210D0201-EU

LS210D0301-EU

## About Buffalo

Buffalo Technology is a leading global provider of award-winning storage, networking, memory, and multimedia solutions for the home and small business environments as well as for system builders and integrators. With more than three decades of networking and computer peripheral experience, Buffalo has proven its commitment to delivering innovative solutions that have put the company at the forefront of infrastructure technology.

© Buffalo Inc. 2014. BUFFALO logo, AirStation, Nfiniti, AOSS, TeraStation, LinkStation, DriveStation, and MiniStation are either trademarks or registered trademarks of Melco Holdings Inc. or Buffalo Inc. Microsoft Windows and Microsoft logo are either registered trademarks or trademarks of Microsoft corporation in United States and/or other countries. The names and logos of other companies mentioned herein belong to their respective owners. The information within this datasheet is subject to change without notice. All rights reserved. E & OE.