



## Professional Series LED Handlamps



### Description

These LED handlamps are ideal for use where additional or focused light is required. Supplied with a 5m lead and are resistant to oil and water.

### Features

- 4 x 3W high power LEDs
- 400lm light output
- High quality PVC body with polycarbonate lens
- Strong hook on top for suspension
- On/off switch on handle
- Water and oil resistant
- Will not roll on inclined surfaces
- Complete with 5m lead
- 24V and 110-230V versions available
- 110-230V version supplied fitted with 230V 13A plug – will operate on 110V when connected to a suitable 110V supply

### Range

P2 Professional LED Handlamp 24V	P200
P3 Professional LED Handlamp 110-230V	P300

### Technical Specification

Voltage	P200	24V~ 50Hz
	P300	110-230V~ 50Hz
Lamp Type	4 x 3W LED	
Light Output	400lm	
Cable Length	5m	
Plug	P200	Bare ends
	P300	13A BS1363 (3A fuse)
Light colour temperature	6500K	
IP Rating	IP40	

### Standards

- BS EN 55015:2013
- BS EN 61547:2009
- BS EN 61000-3-2:2006 +A1:2009 +A2:2009
- BS EN 61000-3-3:2013
- RoHS Directive 2011/65/EU