



## Technical data

### NATV15XLL/3AS

Roller follower with inner ring

#### PRODUCT DEFINITION

|                                               |          |
|-----------------------------------------------|----------|
| Brand                                         | NTN      |
| d - Internal diameter                         | 15 mm    |
| D - External diameter                         | 35 mm    |
| C - Width of bearing, drawn cup or outer ring | 18 mm    |
| F - Under roller diameter                     | 20 mm    |
| B - Bearing/Inner ring width                  | 19 mm    |
| e - Inlet diameter of roller or washer        | 27 mm    |
| Bearing with/without cage                     | Sans     |
| Radial clearance class                        | CN       |
| Precision class                               | P0       |
| Mass                                          | 0,102 kg |

#### PRODUCT PERFORMANCE

|                                            |             |
|--------------------------------------------|-------------|
| Cr - Dynamic load rating                   | 18400000 mN |
| C0r - Static load rating                   | 38000000 mN |
| Track load capacity cylindrical outer ring | 11900000 mN |
| N lim - Grease lubrication limit speed     | 30000 °/s   |
| Tmin - Min operating temperature           | 253,15 °K   |
| Tmax - Max operating temperature           | 373,15 °K   |



#### NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00  
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072  
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15